

# CORiTEC 150i series

## WHAT ARE THE DIFFERENCES?



CORiTEC  
150i PRO



CORiTEC  
150i dry



CORiTEC  
150i dry eco



CORiTEC  
150i PRO



CORiTEC  
150i dry



CORiTEC  
150i dry eco

Number of axes	5	5	5
Number of tool positions	10	10	10
Spindle power / rpm	750 W / 100.000 rpm	750 W / 100.000 rpm	750 W / 100.000 rpm
Zero-Point-Clamping (manually)	✓	✓	✓
Dry processing	✓	✓	✓
Wet processing	✓	-	-
98 mm blank processing	✓	✓	✓
CAD/CAM blocks/glass-ceramics	✓	✓ (dry only)	✓ (dry only)
Premilled abutments	✓	-	-
Control-PC	integrated	integrated	external PC required
10" HD touchscreen	✓	✓	-
Coolant tank	integrated	-	-
Dust tray	-	✓	optionally
Ionizer	✓	✓	optionally
LED statusbar	✓	✓	optionally
Auto-calibration set	✓	✓	optionally
Compressed air	3 bar external air required	3 bar external air required	3 bar external air required
Collet	3 mm stainless steel	3 mm steel	3 mm steel
Pure Water processing	✓	-	-
C-Clamp processing (optionally)	✓	✓	✓
Integration in exocad® & 3shape™ chairside workflow	-	-	-
Turning processing (universal fixture required)	optionally	optionally	optionally
iCAM HD (in preparation)	Including 3 month test period iCAM HD (Subscription license) free of charge.		

Adapters			
98 mm blank holder	included	included	included
Universal fixture for glass-ceramic and premilled abutments	available as accessory	available as accessory (dry processing of CAD/CAM blocks only)	available as accessory (dry processing of CAD/CAM blocks only)
3-fold glass-ceramic holder (for 98 mm blank holder)	available as accessory	available as accessory (dry only processing)	available as accessory (dry only processing)
6-fold glass-ceramic holder (for 98 mm blank holder)	available as accessory	available as accessory (dry only processing)	available as accessory (dry only processing)
C-Clamp blank holder	available as accessory	available as accessory	available as accessory
Nt-trading preform blank holder 6-fold (for 98 mm blank holder)	available as accessory	n.a.	n.a.
Medentika preface blank holder 6-fold (for 98 mm blank holder)	available as accessory	n.a.	n.a.
DESS premilled blank holder 6-fold (for 98 mm blank holder)	available as accessory	n.a.	n.a.
Zfx premilled blank holder 6-fold (for 98 mm blank holder)	available as accessory	n.a.	n.a.
Glass-ceramic adapter for universal fixture	available as accessory	available as accessory (dry only processing)	available as accessory (dry only processing)
Nt-trading preform adapter for universal fixture	available as accessory	n.a.	n.a.
Medentika preface adapter for universal fixture	available as accessory	n.a.	n.a.
DESS premilled adapter for universal fixture	available as accessory	n.a.	n.a.
Zfx premilled adapter for universal fixture	available as accessory	n.a.	n.a.